

FLEXTREME 450/750 V

Highly flexible oil and heat resistant cable



DESCRIPTION

A highly flexible oil and heat resistant cable. For use where the mechanical stresses are of moderate character, in dry, damp or explosive areas, outdoors, eg in agriculture operating buildings and for temporary installations at construction sites. Even for the installation of temporary buildings and work sheds.

STANDARDS, CERTIFICATIONS AND APPROVALS



SS-EN 50525-2-21

Construction standard

Synonyms

Flextrema H07RN-F

Cable marking example

FLEXTREME H07RN-F 450/750 V 5G25 mm²

Conductor material

Copper

Core insulation material

EPDM rubber

Material inner sheath

Rubber

Material outer sheath

EPDM rubber

Cable shape

Round

Max. conductor temperature

85

PRODUCT LIST

Product name	Outer diameter [mm]	Cable weight [kg/km]	Delivery length [m]	Packaging	External article code	SAP code
FLEXTREME H07RN-F 4G25	30.66	1,676	500	K12	0540195	20031893
FLEXTREME H07RN-F 4G35	34.19	2,187	500	K14	0540205	20031894
FLEXTREME H07RNF 4G50	38.6	2,998	500	K16	0540215	20031895
FLEXTREME H07RN-F 4G70	42.96	3,973	500	K18	0540225	20031889
FLEXTREME H07RN-F 4G95	49.1	5,209	500	K20	0540235	20031890
FLEXTREME H07RN-F 4G120	53.88	6,460	500	K20	0540245	20031891
FLEXTREME H07RN-F 5G25	33.89	2,076	500	K14	0540395	20031896
FLEXTREME 07RN-F 5G35	38.02	2,728	500	K16	0540405	20031897
FLEXTREME H07RN-F 5G50	43.38	3,787	500	K18	0530435	20031898
FLEXTREME H07RN-F 5G70	48.47	5,010	500	K20	0530475	20016925
FLEXTREME H07RN-F 5G95	54	6,380	500		0530445	20111116