

ARE4H5EX 12/20KV 3X1X120RM CPR F



CURRENT CARRYING CAPACITY

Cross-section (mm ²)	Direct in ground trefoil (A)
70	200
120	290
150	320
185	360
240	420

Ground temperature: 20°C

Depth of laying: 1,2 m; Soil resistivity, moist: 1 K.m/W

Technical data, dimensions and weights are subject to change. All sizes and values without tolerances are reference values. Specifications are for products supplied by Prysmian: any modification or alteration of products may give different results. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is correct to the best of our knowledge at the time of publication. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by Prysmian. © All rights reserved by Prysmian 2024 · www.prysmian.com