


## UC500 AS23 Cat.6A F/FTP 4P LSHF E<sub>ca</sub>

Data horizontal cable Cat.6A F/FTP



**Eca**  
CPR

### CABLE FEATURES

Draka installation cable for indoor use UC500 AS23 Cat.6A F/FTP 4P LSHF Eca

- Copper data cable of Cat.6A for structured cabling with a bandwidth of 500 MHz.
- With foil pair shielding and with overall foil shielding, the cable is double-shielded.
- The 4-pair simplex installation cable with 8 copper wires AWG23 is suitable for the connection of sockets, patch fields and modules, also with IDC technology, for installation in buildings, in ducts and flush mounting
- the product exceeds the requirements of EN50173-1; EN50288-10-1, ISO/IEC11801; IEC61156-5 and IEEE802.3af/at/bt.
- The jacket is made of halogen-free, flame-retardant material according to IEC60332-1; IEC60754-2; IEC61034; EN50399 and Euro fire class Eca.
- the product fulfills segregation class C according to EN50174 with a coupling attenuation of 55 dB.
- The cable is future-proof for all applications according to Class C, D, E and EA and suitable for the operation of PoE and PoE+ over a channel length of up to 100m. It is suitable for the following applications: Telephony, Ethernet, Fast Ethernet, Gigabit Ethernet and 10Gigabit Ethernet, 10BaseT, 100BaseT, 1000BaseT, 1GBase-T, 10GBaseT or up to 10,000 Mbit/s.

Latest version of this data sheet is available for download: [ProductFamily238744](#)

### GENERAL INFO

Primary (Campus), Secondary (Riser), Tertiary (Horizontal); IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; IEEE802.5; ISDN, TPDDI, ATM, CATV, IP Cameras, Broadband Video, SOHO-Cabling; Power over Ethernet (PoE) / Type 1-4

### CERTIFICATIONS AND DESIGN STANDARDS



**ISO/IEC 11801**  
**IEC 61156-5**  
**IEEE 802.3 af/at/bt**

Generic telecom cabling for customer premises  
Datacom cables  
Power over Ethernet (PoE) / Type 1-4 according to IEEE 802.3 af/at/bt

## CABLE CONSTRUCTION

Conductor category	Class 1 = solid
Conductor material	Copper
Conductor surface	Bare
AWG size	23
Core insulation material	Foam-skin-PE
Nominal diameter over insulation [mm]	1.4
Screen over stranding element	Foil
Number of stranding elements	4
Identification of stranding elements	Core colors: blue/white; orange/white; green/white; brown/white
Screen material	Aluminium
Screen over stranding	Foil
Material outer sheath	Halogenfree polymer
Cable shape	Round
Nominal outer diameter [mm]	7.1

## APPLICATION PROPERTIES

Operation temperature (min) [°C]	-20	(max) [°C]	60
Installation temperature (min) [°C]	0	(max) [°C]	50
Bending radius (rule)	Installation: 8 x outer diameter; Installed: 4 x outer diameter		

## FIRE PROPERTIES

Flame retardant	In accordance with EN/IEC 60332-1-2
Halogen free	acc. IEC/EN 60754-1/2
Low smoke	acc. IEC/EN 61034-2
Reaction-to-fire class (acc. EN 13501-6)	Eca
Smoke development class (acc. EN 13501-6)	Not applicable
Euro class flaming droplets/particles (acc. EN 13501-6)	Not applicable
Euro class acidity (acc. EN 13501-6)	Not applicable
Fire load [MJ/km]	495
DOP number	1001431

## ELECTRICAL PROPERTIES

Test voltage [kV]	1
Category	6A (IEC)
NVP value [%]	79
Propagation delay (max) [ns/100m]	427
Delay skew (max) [ns/100m]	12
Characteristic impedance [Ohm]	100
Nominal mutual capacitance [pF/m]	43
Loop resistance [Ohm]	154
Coupling attenuation [dB]	75
Insulation resistance [MΩ·km]	5,000
Transfer impedance at 10 MHz [mOhm/m]	50
Segregation classification (acc. EN 50174-2)	c

## CAT 6A TRANSMISSION CHARACTERISTICS (AT 20°C)

Frequency (MHz)	Attenuation (dB/100 m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100 m)	PS-ACR (dB/100 m)	ACRF (dB/100m)	PS-ACRF (dB)	Return Loss (dB)
1	1.8	100	97	98	95	105	102	-
4	3.3	100	97	97	94	105	102	27
10	5.1	100	97	95	92	97	94	30
16	6.5	100	97	94	91	93	90	30
20	7.2	100	97	93	90	91	88	30
31.2	9.1	100	97	91	88	87	84	30
62.5	13.2	100	97	87	84	81	78	30
100	17	100	97	83	80	77	74	30
125	19.2	95	92	76	73	75	72	26
155.5	21.7	93	90	71	68	73	70	26
175	23.1	93	90	70	67	72	69	25
200	25	92	89	67	64	71	68	25
250	28.3	90	87	62	59	69	66	24
300	31.5	89	86	58	55	67	64	24
400	37.2	87	84	50	47	65	62	23
500	42.5	86	83	44	41	63	60	22

## PRODUCT ORDER DATA

Product name	Nominal outer diameter [mm]	Max. tensile strength during installation [kN]	Copper weight [kg/km]	SAP code	Packaging type	Standard packaging quantity	Gross weight
UC500 AS 23 Cat.6A F/FTP 4P LSHF Eca	7.1	0.1	24	60009617	Drum	1	50.9
UC500 AS 23 Cat.6A F/FTP 4P LSHF Eca	7.1	0.1	24	60011268	Drum	500	25.8
UC500 AS 23 Cat.6A F/FTP 4P LSHF Eca	7.1	0.1	24	60011267	Drum	1,000	50.9

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.