


E20: UC^{FIBRE} I/O CT LSHF-FR D_{ca} 3.0kN

3000N, CT up to 24 fibres, glass yarns, FireRes® sheath



Dca
CPR

GENERAL INFO

Fibre optic cable with central loose tube filled with gel and up to 24 fibres for structured cabling. It features 3000N tensile strength for indoor and outdoor applications and dielectric design with glass yarns armour, longitudinally water blocked, rodent-proof and FireRes® flame retardant sheath. Used outdoors for underground installation in ducts and as a flame-retardant cable indoors. DIN/VDE: U-DQ(ZN)BH

More information on fiber optic cable applications: [read more](#)

Latest version of this data sheet is available for download: [ProductFamily239116](#)

CERTIFICATIONS AND DESIGN STANDARDS



ISO/IEC 11801
EN 50173
EN 50575
IEC 60794-1-1
IEC 60794-6-10

Generic telecom cabling for customer premises
Information technology - Generic cabling systems
Cables in construction works subject to reaction to fire
Generic Specification Fibre Optic Cables
Family specification for universal indoor-outdoor cables

APPLICATION PROPERTIES

Resistant to UV	UV stabilised
Outdoor installation With rodent protection	Yes
Operation temperature (min) [°C]	-30 and (max) [°C] 70
Installation temperature (min) [°C]	-15 and (max) [°C] 60
Storage temperature (min) [°C]	-30 and (max) [°C] 60
Bending radius (rule)	During installation (loaded) = 20xOD, Permanent (unloaded) = 10xOD

CABLE CONSTRUCTION

Type of tube	Gel-filled loose tube Ø2.8mm for 2fo up to 24fo
Longitudinal water blocking construction	Yes
Rip cord	Yes
Armouring/reinforcement	E-glass yarns
Material outer sheath	Low smoke zero halogen, FireRes®
Cable marking example	Draka UCFIBRE I/O CT LSHF-FR Dca-s2-d1-a1 3.0 kN 'Fibre count ' 'Fibre type ' 'Fibre brand ' 'Item No ' 'Factory No ' 'Batch Number ' 'Meter mark ' U-DQ(ZN)BH 'Fibre count ' 'Fibre family ' 'Core diameter ' /125 'Transmission Class '

IDENTIFICATION

Fibre colour code	1 Red	13 Red w/mark every 70mm
<i>in accordance with IEC 60794-2 and VDE 0888 read more</i>	2 Green	14 Green w/mark every 70mm
	3 Blue	15 Blue w/mark every 70mm
	4 Yellow	16 Yellow w/mark every 70mm
	5 White	17 White w/mark every 70mm
	6 Grey	18 Grey w/mark every 70mm
	7 Brown	19 Brown w/mark every 70mm
	8 Violet	20 Violet w/mark every 70mm
	9 Turquoise	21 Turquoise w/mark every 70mm
	10 Black	22 White w/mark every 35mm
	11 Orange	23 Orange w/mark every 70mm
	12 Pink	24 Pink w/mark every 70mm
Sheath color	Cable with SM fibres: BendBrightXSG.657.A2, BendBright G.657.A1 Yellow, RAL 1018 Cable with mixed fibre types (hybrid) Blue, RAL 5015 Cable with OM1 Grey, RAL 7037 Cable with MaxCap-BendBright-OM2 Orange, RAL 2009 Cable with MaxCap-BendBright-OM3 Aqua, RAL 6027 Cable with MaxCap-BendBright-OM4 Erika-Violet, RAL 4003 Cable with BendBright WideCap-OM5 Lime-Green, RAL 6039	

MECHANICAL PROPERTIES

Nominal outer diameter		7.3 mm
Cable weight		64.5 kg/km
Fire load		1,373 MJ/km
Crush test (1min, reversible)	IEC 60794-1-21 E3	3,500 N/10cm
Torsion test	IEC 60794-1-21 E7	5 cycles ±1turn
Impact test	IEC 60794-1-21 E4	20 N·m
Max. tensile strength during installation	IEC 60794-1-21 E1	3,000 N
Permanent tensile strength	IEC 60794-1-21 E1	1,000 N
Kink test	IEC 60794-1-21 E10	The cables do not form a kink when a loop is drawn together to a diameter 20 times the cable nominal diameter
Water penetration	IEC 60794-1-22 F5B	No water on free end

FIRE PROPERTIES

Flame retardant	acc. IEC/EN 60332-1-2
Halogen free	acc. IEC/EN 60754-2
Low smoke	Yes
The reaction to fire according to the EN 50575	Dca - s2, d1, a1

ORDERING DETAILS

Product name	Number of fibres	Category (fibre)	Fibre datasheet	DOP number	SAP code
UCFIBRE I/O CT LSHF-FR 3.0kN 4 SM7A1 YL	4	OS2	C17	1006747	60066049
UCFIBRE I/O CT LSHF-FR 3.0kN 6 SM7A1 YL	6	OS2	C17	1011950	60090757
UCFIBRE I/O CT LSHF-FR 3.0kN 8 SM7A1 YL	8	OS2	C17	1006748	60066050
UCFIBRE I/O CT LSHF-FR 3.0kN 12 SM7A1 YL	12	OS2	C17	1004838	60060781
UCFIBRE I/O CT LSHF-FR 3.0kN 16 SM7A1 YL	16	OS2	C17	1014816	60096654
UCFIBRE I/O CT LSHF-FR 3.0kN 24 SM7A1 YL	24	OS2	C17	1011803	60090670
UCFIBRE I/O CT LSHF-FR 3.0kN 4 SM7B.P YL	4	OS2	C25	1004829	60060276
UCFIBRE I/O CT LSHF-FR 3.0kN 8 SM7B.P YL	8	OS2	C25	1004822	60060231
UCFIBRE I/O CT LSHF-FR 3.0kN 12 SM7B.P	12	OS2	C25	1004821	60060230
UCFIBRE I/O CT LSHF-FR 3.0kN 6 OM2B OR	6	OM2	C34	1004848	60061208
UCFIBRE I/O CT LSHF-FR 3.0kN 8 OM2B OR	8	OM2	C34	1015113	60094438
UCFIBRE I/O CT LSHF-FR 3.0kN 12 OM2B OR	12	OM2	C34	1006017	60061209
UCFIBRE I/O CT LSHF-FR 3.0kN 24 OM2B OR	24	OM2	C34	1008106	60073128
UCFIBRE I/O CT LSHF-FR 3.0kN 4 OM3B AQ	4	OM3	C31	1004823	60060232
UCFIBRE I/O CT LSHF-FR 3.0kN 6 OM3B AQ	6	OM3	C31	1004849	60061211
UCFIBRE I/O CT LSHF-FR 3.0kN 8 OM3B AQ	8	OM3	C31	1004824	60060271
UCFIBRE I/O CT LSHF-FR 3.0kN 12 OM3B AQ	12	OM3	C31	1004825	60060272
UCFIBRE I/O CT LSHF-FR 3.0kN 24 OM3B AQ	24	OM3	C31	1008341	60073151
UCFIBRE I/O CT LSHF-FR 3.0kN 4 OM4B EV	4	OM4	C32	1004826	60060273
UCFIBRE I/O CT LSHF-FR 3.0kN 6 OM4B EV	6	OM4	C32	1005412	60062233
UCFIBRE I/O CT LSHF-FR 3.0kN 8 OM4B EV	8	OM4	C32	1004827	60060274
UCFIBRE I/O CT LSHF-FR 3.0kN 12 OM4B EV	12	OM4	C32	1004828	60060275
UCFIBRE I/O CT LSHF-FR 3.0kN 24 OM4B EV	24	OM4	C32	1008138	60073153
UCFIBRE I/O CT LSHF-FR 3.0kN 12 OM5B LI	12	OM5	C39	1016580	60104987
UCFIBRE I/O CT LSHF-FR 3.0kN 6 MM61 SL	6	OM1	C02	1004852	60061214
UCFIBRE I/O CT LSHF-FR 3.0kN 12 MM61 SL	12	OM1	C02	1004853	60061215
UCFIBRE I/O CT LSHF-FR 3.0kN 24 MM61 SL	24	OM1	C02	1008271	60073152

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.