


UC900 HS23 Cat.7 S/FTP 2X4P LSHF D_{ca}

Data horizontal cable Cat.7 S/FTP



CABLE FEATURES

Prysmian installation cable for indoor use UC900 HS23 Cat.7 S/FTP 2X4P LSHF Dca

- Copper data cable of Cat.7 for structured cabling with a bandwidth of 1000 MHz.
- The cable is double-shielded with foil pair shielding and high-quality braided cover.
- The 2x4-pair duplex installation cable with 2x8 copper wires AWG23 is suitable for the connection of sockets, patch fields and modules, also with LSA technology, for installation in buildings, in ducts and flush-mounted
- the product exceeds the requirements of EN50173-1; EN50288-4-1, ISO/IEC11801; IEC61156-5 and IEEE802.3af/at/bt.
- The jacket is made of halogen-free, flame-retardant material according to IEC60332-1; IEC60754-2; IEC61034; EN50399 and Euro fire class Dca s2 d1 a1.
- With a coupling attenuation of 80 dB, the shielding fulfills segregation class D according to EN50174.
- The cable is future-proof for all applications according to Class C, D, E, EA and F and suitable for the operation of PoE and PoE+ over a channel length of up to 100m. It is suitable for the following applications: Telephony, Ethernet, Fast Ethernet, Gigabit Ethernet and 10Gigabit Ethernet, 10BaseT, 100BaseT, 1000BaseT, 1GBase-T, 10GBaseT or up to 10,000Mbit/s.

Latest version of this data sheet is available for download: [ProductFamily239073](#)

GENERAL INFO

AWG23 Bare copper wire, Al-laminated plastic foil, 2x4 pairs (PiMF) to the core, copper braid-tinned, LSHF sheath, Dca Primary (Campus), Secondary (Riser), Tertiary (Horizontal) IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T IEEE 802.5 16 MB; ISDN; TPDDI; ATM Power over Ethernet (PoE) / Type 1-4

CERTIFICATIONS AND DESIGN STANDARDS



EN 50288-4-1
IEC 61156-5
ISO/IEC 11801
EN 50173

Datacom cables up to 600 MHz
 Datacom cables
 Generic telecom cabling for customer premises
 Information technology - Generic cabling systems

CABLE CONSTRUCTION(AC)

Conductor category	Class 1 = solid
Conductor material	Copper
Conductor surface	Bare
AWG size	23
Core insulation material	Foam-skin-PE
Nominal diameter over insulation [mm]	1.4
Screen over stranding element	Foil
Number of stranding elements	8
Kennzeichnung der Verseilelemente	Aderfarben: blau/weiß; orange/weiß; grün/weiß; braun/weiß; identisch für beide Einzelkabel
Screen material	Copper, tinned
Screen over stranding	Braiding
Material outer sheath	Halogenfree polymer
Cable shape	Twin
Cable width approx. [mm]	14.6
Cable height approx. [mm]	7.2

APPLICATION PROPERTIES

Operation temperature (min) [°C]	-20	(max) [°C]	60
Installation temperature (min) [°C]	0	(max) [°C]	50
Bending radius (rule)	Installation: 8 x outer diameter; Installed: 4 x outer diameter		

FIRE PROPERTIES

Flame retardant	In accordance with EN/IEC 60332-1-2
Halogen free	acc. IEC/EN 60754-1/2
Low smoke	acc. IEC/EN 61034-2
Reaction-to-fire class (acc. EN 13501-6)	Dca
Smoke development class (acc. EN 13501-6)	s2
Euro class flaming droplets/particles (acc. EN 13501-6)	d1
Euro class acidity (acc. EN 13501-6)	a1
Fire load [MJ/km]	1,180
DOP number	1002809

ELECTRICAL PROPERTIES

Test voltage [kV]	1
Category	7
NVP value [%]	79
Propagation delay (max) [ns/100m]	427
Delay skew (max) [ns/100m]	12
Characteristic impedance [Ohm]	100
Nominal mutual capacitance [pF/m]	43
Loop resistance [Ohm]	154
Coupling attenuation [dB]	80
Insulation resistance [MΩ·km]	5,000
Transfer impedance at 10 MHz [mOhm/m]	10
Segregation classification (acc. EN 50174-2)	d

CAT.7 TRANSMISSION CHARACTERISTICS (AT 20°C)

Frequency (MHz)	Attenuation (dB/100 m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100 m)	PS-ACR (dB/100 m)	ACRF (dB/100m)	PS-ACRF (dB)	Return Loss (dB)
1	1.8	100	97	98	95	105	102	-
4	3.3	100	97	97	94	105	102	27
10	5.2	100	97	95	92	97	94	30
16	6.6	100	97	93	90	93	90	30
20	7.4	100	97	93	90	91	88	30
31.2	9.3	100	97	91	88	87	84	30
62.5	13.4	100	97	87	84	81	78	30
100	17.2	100	97	83	80	77	74	30
125	19.4	95	92	76	73	75	72	26
155.5	21.8	94	91	72	69	73	70	26
175	23.3	93	90	70	67	72	69	25
200	25.1	92	89	67	64	71	68	25
250	28.4	90	87	62	59	69	66	24
300	31.4	89	86	58	55	67	64	24
450	39.5	87	84	48	45	64	61	23
600	46.6	85	82	38	35	61	58	22
750	53.2	83	80	30	27	59	56	21
900	59.2	82	79	23	20	58	55	20
1000	63.1	81	78	18	15	57	54	20

PRODUCT ORDER DATA

Product name	Max. tensile strength during installation [kN]	Copper weight [kg/km]	SAP code	Packaging type	Standard packaging quantity	Gross weight
UC900 HS23 Cat.7 S/FTP 2X4P LSHF Dca	0.3	52	60091276	Drum	100	
UC900 HS23 Cat.7 S/FTP 2X4P LSHF Dca	0.3	52	60060189	Drum	500	56.11

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.