

E25: UC^{FIBRE} I/O CT LSHF-FR B2_{ca} 3.0kN

3000N, CT up to 24 fibres, glass yarns, FireRes® sheath



B2_{ca}
CPR

GENERAL INFO

Fibre optic cable with central loose tube filled with gel and up to 24 fibres for structured cabling. It features 3000N tensile strength for indoor and outdoor applications and dielectric design with glass yarns armour, longitudinally water blocked, rodent-proof and FireRes® sheath with very high flame retardant performance, ideal for indoor installations. It is also well suited for installation in ducts and on trays indoor and limited outdoor use in ducts. This unitube cable can be used for LAN and WAN backbones, telecom access lines, fibre to business and fibre to the building drop connections; as well as fibre to the home drop and access connections. DIN/VDE: U-DQ(ZN)BH

More information on fiber optic cable applications: [read more](#)

Latest version of this data sheet is available for download: [ProductFamily239159](#)

CERTIFICATIONS AND DESIGN STANDARDS




ISO/IEC 11801
EN 50173
EN 50575
IEC 60794-1-1
IEC 60794-6-10

Generic telecom cabling for customer premises
Information technology - Generic cabling systems
Cables in construction works subject to reaction to fire
Generic Specification Fibre Optic Cables
Family specification for universal indoor-outdoor cables

CABLE CONSTRUCTION

Type of tube	Gel-filled loose tube Ø2.8mm for 2fo up to 24fo
Longitudinal water blocking construction	Yes
Rip cord	Yes
Armouring/reinforcement	E-glass yarns
Material outer sheath	Low smoke zero halogen, FireRes®
Cable marking example	Draka UC ^{FIBRE} I/O CT LSHF-FR B2ca-s1a-d1-a1 3.0 kN 'Fibre count' 'Fibre type' 'Fibre brand' 'Item No' 'Factory Code' 'Batch Number' 'Meter mark' U-DQ(ZN)BH 'Fibre count' 'Fibre family' 'Mode field diameter' /125 'Transmission Class'



IDENTIFICATION

Fibre colour code	1 Red	13 Red w/mark every 70mm
<i>in accordance with IEC 60794-2 and VDE 0888 read more</i>	2 Green	14 Green w/mark every 70mm
	3 Blue	15 Blue w/mark every 70mm
	4 Yellow	16 Yellow w/mark every 70mm
	5 White	17 White w/mark every 70mm
	6 Grey	18 Grey w/mark every 70mm
	7 Brown	19 Brown w/mark every 70mm
	8 Violet	20 Violet w/mark every 70mm
	9 Turquoise	21 Turquoise w/mark every 70mm
	10 Black	22 White w/mark every 35mm
	11 Orange	23 Orange w/mark every 70mm
	12 Pink	24 Pink w/mark every 70mm
Sheath color	Cable with SM fibres: BendBrightXSG.657.A2, BendBright G.657.A1 Yellow, RAL 1018 Cable with mixed fibre types (hybrid) Blue, RAL 5015 Cable with OM1 Grey, RAL 7037 Cable with MaxCap-BendBright-OM2 Orange, RAL 2009 Cable with MaxCap-BendBright-OM3 Aqua, RAL 6027 Cable with MaxCap-BendBright-OM4 Erika-Violet, RAL 4003 Cable with BendBright WideCap-OM5 Lime-Green, RAL 6039	

APPLICATION PROPERTIES

Resistant to UV	UV stabilised
Outdoor installation With rodent protection	Yes
Operation temperature (min) [°C]	-40 and (max) [°C] 70
Installation temperature (min) [°C]	-15 and (max) [°C] 60
Storage temperature (min) [°C]	-30 and (max) [°C] 60
Bending radius (rule)	During installation (loaded) = 20xOD, Permanent (unloaded) = 10xOD

MECHANICAL PROPERTIES

Nominal outer diameter	7.5 mm
Cable weight	73 kg/km
Fire load	1,220 MJ/km
Crush test (Imin, reversible)	IEC 60794-1-21 E3 3,000 N/10cm
Torsion test	IEC 60794-1-21 E7 5 cycles ±1turn
Impact test	IEC 60794-1-21 E4 20 N·m
Max. tensile strength during installation	IEC 60794-1-21 E1 3,000 N
Permanent tensile strength	IEC 60794-1-21 E1 1,000 N
Kink test	IEC 60794-1-21 E10 The cables do not form a kink when a loop is drawn together to a diameter 20 times the cable nominal diameter
Water penetration	IEC 60794-1-22 F5B No water on free end

FIRE PROPERTIES

Flame retardant	acc. IEC/EN 60332-1-2, IEC/EN 60332-3-24
Halogen free	acc. IEC/EN 60754-2
Low smoke	acc. IEC/EN 61034-2
The reaction to fire according to the EN 50575	B2ca - s1a, d1, a1

ORDERING DETAILS

Product name	Number of fibres	Category (fibre)	Fibre datasheet	DOP number	SAP code
UCFIBRE I/O CT LSHFFR B2 3KN 4 SM7A1 YL	4	OS2	C17	1010670	60083197
UCFIBRE I/O CT LSHF-FR B2 3KN 6 SM7A1 YL	6	OS2	C17	1015950	60101149
UCFIBRE I/O CT LSHFFR B2 3KN 8 SM7A1	8	OS2	C17	1011991	60090925
UCFIBRE I/O CT LSHFFR B2 3KN 12 SM7A1 YL	12	OS2	C17	1010671	60083198
UCFIBRE I/O CT LSHFFR B2 3KN 24 SM7A1 YL	24	OS2	C17	1010672	60083199
UCFIBRE I/O CT LSHFFR B2 3KN 8 OM2B OR	8	OM2	C34	1011980	60090910
UCFIBRE I/O CT LSHFFR B2 3KN 12 OM2B OR	12	OM2	C34	1011990	60090911
UCFIBRE I/O CT LSHFFR B2 3KN 24 OM2B OR	24	OM2	C34	1011982	60090912
UCFIBRE I/O CT LSHFFR B2 3KN 4 OM3B AQ	4	OM3	C31	1010613	60083160
UCFIBRE I/O CT LSHFFR B2 3KN 8 OM3B AQ	8	OM3	C31	1011983	60090913
UCFIBRE I/O CT LSHFFR B2 3KN 12 OM3B AQ	12	OM3	C31	1011299	60087031
UCFIBRE I/O CT LSHFFR B2 3KN 24 OM3B AQ	24	OM3	C31	1010612	60083159
UCFIBRE I/O CT LSHFFR B2 3KN 2 OM4B 4003	2	OM4	C32	1015104	60098236
UCFIBRE I/O CT LSHFFR B2 3KN 4 OM4B 4003	4	OM4	C32	1015200	60098261
UCFIBRE I/O CT LSHFFR B2 3KN 8 OM4B EV	8	OM4	C32	1011984	60090914
UCFIBRE I/O CT LSHFFR B2 3KN 12 OM4B EV	12	OM4	C32	1011681	60083157
UCFIBRE I/O CT LSHFFR B2 3KN 24 OM4B EV	24	OM4	C32	1011090	60085428

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.