


UC400 23 Cat.6 U/UTP 4P PE

Data horizontal cable Cat.6 U/UTP for outdoor installations



GENERAL INFO

Primary (Campus), Secondary (Riser), Tertiary (Horizontal) IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T; IEEE 802.5 ISDN, TPDDI, ATM, CATV, IP Cameras, Broadband Video, SOHO-Cabling; Power over Ethernet (PoE) / Type 1-4

CABLE FEATURES

Prysmian installation cable for outdoor use UC400 23 Cat.6 U/UTP 4P PE

- Copper data cable of category 6 for structured cabling with a bandwidth of 400 MHz.
- the cable is unshielded.
- The 4-pair simplex installation cable with 8 copper wires AWG23 is suitable for the connection of sockets, patch fields and modules, also with IDC technology, for installation in buildings, in fire protection ducts or flush-mounted and outdoors for direct burial
- the product exceeds the requirements of EN50173-1; EN50288-6-1, ISO/IEC11801; IEC61156-5 and IEEE802.3af/at/bt.
- The jacket is made of halogen-free polyethylene.
- the product fulfills segregation class B according to EN50174 with a coupling attenuation of 40 dB.
- The cable is future-proof for all applications according to Class C, D, and E and suitable for the operation of PoE and PoE+ over a channel length of up to 100m. It is suitable for the following applications: Telephony, Ethernet, Fast Ethernet and Gigabit Ethernet, 10BaseT, 100BaseT, 1000BaseT, 1GBase-T or up to 1,000Mbit/s.

Latest version of this data sheet is available for download: [ProductFamily239222](#)

CERTIFICATIONS AND DESIGN STANDARDS



APPLICATION PROPERTIES

Operation temperature (min) [°C]	-40	(max) [°C]	60
Installation temperature (min) [°C]	0	(max) [°C]	50
Bending radius (rule)	Installation: 8 x outer diameter; Installed: 4 x outer diameter		

CABLE CONSTRUCTION

Conductor category	Class 1 = solid
Conductor material	Copper
Conductor surface	Bare
AWG size	23
Core insulation material	Polyethylene (PE)
Nominal diameter over insulation [mm]	1.4
Screen over stranding element	None
Number of stranding elements	4
Identification of stranding elements	Core colors: blue/white; orange/white; green/white; brown/white
Screen material	Not applicable
Screen over stranding	None
Material outer sheath	Polyethylene (PE)
Cable shape	Round
Nominal outer diameter [mm]	6.1

ELECTRICAL PROPERTIES

Test voltage [kV]	1
Category	6
NVP value [%]	67
Propagation delay (max) [ns/100m]	535
Delay skew (max) [ns/100m]	20
Characteristic impedance [Ohm]	100
Nominal mutual capacitance [pF/m]	48
Loop resistance [Ohm]	154
Coupling attenuation [dB]	40
Insulation resistance [MΩ·km]	5,000
Transfer impedance at 10 MHz [mOhm/m]	
Segregation classification (acc. EN 50174-2)	b

PRODUCT ORDER DATA

Product name	Nominal outer diameter [mm]	Max. tensile strength during installation [kN]	Copper weight [kg/km]	SAP code	Packaging type	Standard packaging quantity	Gross weight
UC400 23 Cat.6 U/UTP PE	6.1	0.1	20.5	60011282	Drum	1	36.8
UC400 23 Cat.6 U/UTP PE	6.1	0.1	20.5	60018240	Drum	305	12
UC400 23 Cat.6 U/UTP PE	6.1	0.1	20.5	60011281	Drum	500	19.4
UC400 23 Cat.6 U/UTP PE	6.1	0.1	20.5	60011280	Drum	1,000	36.6

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.

CAT 6 TRANSMISSION CHARACTERISTICS (AT 20°C)

Frequency (MHz)	Attenuation (dB/100 m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100 m)	PS-ACR (dB/100 m)	ACRF (dB/100m)	PS-ACRF (dB)	Return Loss (dB)
1	1.8	100	97	98	95	105	102	-
4	3.3	100	97	97	94	105	102	27
10	5.1	100	97	95	92	97	94	30
16	6.5	100	97	94	91	93	90	30
20	7.3	100	97	93	90	91	88	30
31.2	9.2	100	97	91	88	87	84	30
62.5	13.3	100	97	87	84	81	78	30
100	17.1	100	97	83	80	77	74	30
125	19.3	95	92	76	73	75	72	26
155.5	21.7	93	90	71	68	73	70	26
175	23.2	93	90	70	67	72	69	25
200	25	92	89	67	64	71	68	25
250	28.3	90	87	62	59	69	66	24
300	31.4	89	86	58	55	67	64	24
400	37	87	84	50	47	65	62	23