

## NA2XS(FL)2Y 12/20KV CPR F

Aluminium medium voltage cables 20kV



**F<sub>ca</sub>**  
CPR

Medium voltage cables for rated voltages from 6 kV ( $U_m = 7,2$  kV) up to 30 kV ( $U_m = 36$  kV) used in outdoor applications such as industrial installations and electrical stations. The cables are suitable for laying in ground, in trench or in ducts, in water, free in air or indoors. The ingress of water in case of a damaged outer sheath is limited by the longitudinal and transversal watertight screen area.

Conductor shape round, class 2 = stranded; black outer sheath

### STANDARDS AND CERTIFICATIONS



**RoHS**



**DIN VDE 0295 / DIN EN 60228 / IEC 60228**  
**DIN VDE 0276-620**

**HD 620 S3:2023**

**IEC 60502-2**

**EN 60754-1**

Conductor

Distribution cables for rated voltages from 3,6/6(7,2) up to and including 20,8/36(42) kV

Distribution cables for rated voltages from 3,6/6(7,2) up to and including 20,8/36(42) kV

Cables for rated voltages from 6 kV ( $U_m = 7,2$  kV) up to 30 kV ( $U_m = 36$  kV)

Test on gases evolved during combustion of materials from cables. Halogen acid gas content.

### CABLE DESIGN

Conductor material	Aluminium
Core insulation material	XLPE
Screen construction	Wire screen and counterhelix tape
Screen material	Copper, bare
Longitudinal water blocking screen	Yes
Longitudinal water blocking cable	Yes
Longitudinal water blocking construction	Water swellable tape(s)
Radial water blocking cable	Yes
Protective barrier	Al/PE
Material outer sheath	HDPE
Cable shape	Round

### ELECTRICAL & THERMAL PARAMETERS

Nominal voltage $U_0$ [V]	12,000
Nominal voltage $U$ [V]	20,000
Test voltage [kV]	42
Rated voltage $U_0/U$ ( $U_m$ )	12/20 (24) kV
Max. conductor temperature [°C]	90
Max. conductor temperature at short circuit [°C]	250
Laying temperature (min) [°C]	-20
Laying temperature (max) [°C]	50

Technical data, dimensions and weights are subject to change. All sizes and values without tolerances are reference values. Specifications are for products supplied by Prysmian; any modification or alteration of products may give different results. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is correct to the best of our knowledge at the time of publication. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by Prysmian. © All rights reserved by Prysmian 2024 - [www.prysmian.com](http://www.prysmian.com)

## CHEMICAL PROPERTIES

Halogen free	acc. IEC/EN 60754-1/2
Resistant to UV	Yes
UV resistant	Yes
Silicon free	Yes
Lead free	Yes

## CHARACTERISTICS

Outdoor installation	Yes
Underground installation	Yes
Suitable as installation cable	Yes
Bending radius (rule)	During installing: 15 x D single-core cables

## SUSTAINABILITY COMMITMENT

Our commitment to a low-carbon future remains unwavering as we strive to create sustainable solutions while upholding quality standards. We prioritize sustainability and environmental protection in our daily operations, collaborating with local communities to ensure workplace safety and safeguard the areas we operate in.

Sustainability and environmental responsibility is evident also in our **packaging** solutions across the CEE region. We use fully recyclable drum cover foils to minimize environmental impact. Our packaging for rings is made from 30% recycled materials, supporting a circular economy. Additionally, our boxes are made from recyclable, environment-friendly cardboard, promoting eco-conscious choices. By choosing Prysmian, you are not only selecting high-quality products but also contributing to a greener future.

Check for more details about our sustainability commitment here: [Sustainability report and responsibility](#).



## CABLE PROPERTIES

Basic construction	SAP code	Nominal thickness insulation [mm]	Nominal diameter over insulation [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Bending radius, during laying (min) [mm]	Conductor resistance at 20° C [Ohm/km]	Short circuit current conductor (1sec) [kA]	Short circuit current screen (1sec) [kA]	DOP number
1x70RM/16	20021125	5.5	21.9	31.2	923	468	0.443	6.8	4.7	1003520
1x70RM/25	20204755	5.5	21.9	31.2	1,007	468	0.443	6.8	6.1	1003520
1x95RM/16	20025555	5.5	23.3	32.6	1,045	489	0.32	9.2	5	1003520
1x120RM/25	20204754	5.5	24.7	34	1,218	510	0.253	11.6	6.3	1003520
1x120RM/50	17010102003	5.5	24.5	34	1,460	510	0.253	11.6	10.5	1003520
1x150RM/25	20021127	5.5	26.2	35.5	1,330	532	0.206	14.5	6.4	1003520
1x185RM/16	20455048	5.5	27.6	36.3	1,295	550	0.164	17.9	5.4	
1x185RM/25	20021126	5.5	27.6	36.9	1,481	554	0.164	17.9	6.5	1003520
1x240RM/25	20021128	5.5	30	39.5	1,686	592	0.125	23.1	6.7	1003520
1x240RM/35	17090200038	5.5	30	39.5	1,798	592	0.125	23.1	8.8	1003520
1x240RM/50	17010102006	5.5	30	39.5	1,939	592	0.125	23.1	11.2	1003520
1x300RM/25	20025602	5.5	32.7	41.9	1,942	629	0.1	28.8	6.8	1003520
1x400RM/35	20024537	5.5	35.6	44.9	2,349	674	0.0778	38.3	7.3	1003520
1x500RM/35	20227678	5.5	38.8	48.4	2,723	726	0.0605	47.8	9	1003520
1x630RM/25	17090200088	5.5	41.9	51.7	3,165	776	0.0469	60.2	7.7	1003520
1x630RM/35	17010103035	5.5	41.9	51.7	3,219	776	0.0469	60.2	9.1	1003520
1x800RM/35	17010103039	5.5	46	55.9	3,855	839	0.0367	76.5	8	1003520
1x1000RM/35	17010103040	5.5	50.3	60.2	4,550	903	0.0291	95.3	8.3	1003520

## CURRENT CARRYING CAPACITY

Cross-section (mm²)	Direct in ground trefoil (A)	Direct in ground flat spaced (A)	Air trefoil (A)	Air flat spaced (A)
70	210	237	231	273
95	251	282	280	332
120	285	319	323	384
150	319	352	366	432
185	361	396	420	494
240	417	455	496	581
300	471	510	569	663
400	535	564	660	753
500	609	634	766	866
630	692	700	885	975
800	775	763	1009	1082
1000	857	824	1142	1194
1200	1199	1146	1294	1298

Ground temperature: 20°C; Air temperature: 30°C  
 Depth of laying: 0,7 m; Soil resistivity, moist: 1 K.m/W

Screen bonded at both ends  
 Specifications are subject to change. All sizes and values without tolerances are reference values. Specifications are for products supplied by Prysmian; any modification or alteration of products may give different results. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is correct to the best of our knowledge at the time of publication. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by Prysmian. © All rights reserved by Prysmian 2024 - [www.prysmian.com](http://www.prysmian.com)