


MCCMK-HF C-PRO 3X10/10 RM

Low smoke halogen free screen protected 1 kV power cable



APPLICATION

EMC-protected cable for fixed installation indoors, outdoors and underground, as well as in building structures e.g. directly in concrete (but not in sliding joints). Also for circumstances where it is required to have installation cables with a low emission of smoke and corrosive gases in case of fire.

Discover E Path: baltics.prysmian.com/en/e-path

CERTIFICATIONS AND DESIGN STANDARDS



EN 60228	Conductor standard
IEC 60502-1	1 kV & 3 kV power cables with extruded insulation.
HD 604-51	1 kV & 3,3 kV power cables with special fire performance
EN 50575:2014/A1:2016	Cables for general applications in construction works subject to reaction to fire requirements
HD 308 S2	Identification of cores in cables and flexible cords
EN 60332-1-2	Vertical flame propagation for a single insulated wire or cable
EN 60332-3	Tests on electric and optical fibre cables under fire conditions. Part 3: Test for vertical flame spread of vertically-mounted bunched wires or cables.
IEC 60754	Corrosive gases
IEC 61034	Smoke density
Conductor material	Copper
Conductor surface	Bare
Core insulation material	XLPE
Core identification (acc. HD 308 S2)	Yes
Material outer sheath	Halogenfree polymer
Max. conductor temperature [°C]	90
Max. conductor temperature at short circuit [°C]	250
Permitted cable outer temperature after assembling without vibration (min) [°C]	-40
Resistant to UV	Yes
Permitted cable outer temperature during assembling/handling (min) [°C]	-15
Bending radius (rule)	12x OD
Flame retardant	In accordance with EN 13501-6
Halogen free	Yes
Reaction-to-fire class (acc. EN 13501-6)	Cca
Smoke development class (acc. EN 13501-6)	s1
Euro class flaming droplets/particles (acc. EN 13501-6)	d1
Euro class acidity (acc. EN 13501-6)	a1
UV resistant	Yes

We reserve the right to change as a result of product development and/or changes in product standard.

PRODUCT PROPERTIES

Conductor category	Class 2 = stranded
Shape of conductor	Round
Nominal cross section conductor [mm ²]	10
Number of cores	4
With protective conductor	Yes
Colour outer sheath	Black
Nominal outer diameter [mm]	19
Conductor resistance at 20° C [Ohm/km]	1.83
Current carrying capacity in air [A]	78
Current carrying capacity in ground [A]	77
Cable weight [kg/km]	670
Min. bending radius during installation [mm]	240
DOP number	1003352

Current load in air, installation method E, temperature 25°C

Current load in ground, installation method D2 (directly in ground). Ground temperature 15°C, thermal resistivity 1,0 K·m/W

Item name	EAN-code (GTIN)	Packaging type	Standard packaging quantity
MCCMK-HF C-PRO 3X10/10 RM K11/500 EMC-LI	6430065751465	Drum	500
MCCMK-HF C-PRO 3X10/10 RM K12/1000 EMC-L	6410006019953	Drum	1,000