

RKKN

Jumper wire



GENERAL INFO

APPLICATION

Declaration of Performance (DoP)

Identification of cores

Nominal voltage U [V]

A cross-connection cable for exchanges and distribution boxes.

No CPR-class

SFS 3715

75

CERTIFICATIONS AND DESIGN STANDARDS

RoHS



SFS 3715

IEC 60332-1

IEC 60754-1

IEC 60754-2

CABLE DESIGN

Conductor

Conductor surface

Insulation

Copper

Tinned

Polyamide (PA)

APPLICATION PROPERTIES

Max. conductor temperature [°C]	70
Permitted cable outer temperature after assembling without vibration (min) [°C]	-30
Permitted cable outer temperature during assembling/handling (min) [°C]	-5
Minimum permissible bending radius during laying	1.5 x D under maximum tension 1 x D without tension

FIRE PROPERTIES

Self-extinguishing	Yes
Flame retardant	In accordance with EN/IEC 60332-1-2
Halogen free	acc. IEC/EN 60754-1/2

PRODUCT RANGE

PRODUCT NAME	Snro	DOP number	Diameter over cable [mm]	Weight [kg/km]	Packaging type	Standard delivery length
RKKN 2x0,6	0201279		1.9	6.5	Bobbin	500