

UC1500 SS22 Cat.7A S/FTP 4P PE Outdoor

Data horizontal cable Cat.7A S/FTP



GENERAL INFO

Primary (Campus), Secondary (Riser), Tertiary (Horizontal); IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; IEEE802.5; ISDN, TPDDI, ATM, CATV, IP Cameras, Broadband Video, SOHO-Cabling; Power over Ethernet (PoE) / Type 1-4

CABLE FEATURES

Draka installation cable for indoor use UC1500 SS22 Cat.7A S/FTP PE Outdoor

- Copper data cable of Cat.7A for structured cabling with a bandwidth of 1500 MHz.
- The cable is double-shielded with foil pair shielding and high-quality braided cover.
- The 4-pair simplex installation cable with 8 copper wires AWG22 is suitable for the connection of sockets, patch fields and modules, also with IDC technology, for installation outside buildings
- The product exceeds the requirements of EN50173-1; EN50288-9-1, ISO/IEC11801; IEC61156-5; IEC61156-7 and IEEE802.3af/at/bt.
- The jacket is made of polyethylene.
- With a coupling attenuation of 85 dB, the shielding fulfills segregation class D according to EN50174.
- The cable is future-proof for all applications according to Class C, D, E, EA, F and FA and suitable for operating PoE and PoE+ over a channel length of up to 100m. It is suitable for the following applications: Telephony, Ethernet, Fast Ethernet, Gigabit Ethernet and 10Gigabit Ethernet, 10BaseT, 100BaseT, 1000BaseT, 1GBase-T, 10GBaseT and 25GBaseT up to 30m.

Latest version of this data sheet is available for download: [ProductFamily357300](#)

CERTIFICATIONS AND DESIGN STANDARDS

RoHS



IEC 61156-5

EN 50288-9-1

ISO/IEC 11801

EN 50173

IEEE 802.3 af/at/bt

Datcom cables

Data communications cable shielded up to 1000 MHz

Generic telecom cabling for customer premises

Information technology - Generic cabling systems

Power over Ethernet (PoE) / Type 1-4 according to IEEE 802.3 af/at/bt

APPLICATION PROPERTIES

Operation temperature (min) [°C]

-20 (max) [°C] 60

Installation temperature (min) [°C]

0 (max) [°C] 50

Bending radius (rule)

Installation: 8 x outer diameter; Installed: 4 x outer diameter

CABLE CONSTRUCTION

Conductor category	Class 1 = solid
Conductor material	Copper
Conductor surface	Bare
AWG size	22
Core insulation material	Foam-skin-PE
Nominal diameter over insulation [mm]	1.5
Screen over stranding element	Foil
Number of stranding elements	4
Identification of stranding elements	Core colors: blue/white; orange/white; green/white; brown/white
Screen material	Copper, tinned
Screen over stranding	Braiding
Material outer sheath	Polyethylene (PE)
Cable shape	Round
Nominal outer diameter [mm]	8.9

ELECTRICAL PROPERTIES

Test voltage [kV]	1
Category	7A (IEC)
NVP value [%]	79
Propagation delay (max) [ns/100m]	427
Delay skew (max) [ns/100m]	12
Characteristic impedance [Ohm]	100
Nominal mutual capacitance [pF/m]	43
Loop resistance [Ohm]	128
Coupling attenuation [dB]	85
Insulation resistance [MΩ·km]	5,000
Transfer impedance at 10 MHz [mOhm/m]	5
Segregation classification (acc. EN 50174-2)	d

PRODUCT ORDER DATA

Product name	Nominal outer diameter [mm]	Max. tensile strength during installation [kN]	Copper weight [kg/km]	SAP code	Packaging type	Standard packaging quantity	Gross weight
UC1500 SS22 C7A S/FTP 4P PE	8.9	0.15	40.4	60089979	Drum	1,000	

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.

CAT 7A TRANSMISSION CHARACTERISTICS (AT 20°C)

Frequency (MHz)	Attenuation (dB/100 m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100 m)	PS-ACR (dB/100 m)	ACRF (dB/100m)	PS-ACRF (dB)	Return Loss (dB)
1	1.7	100	97	98	95	100	97	23
4	3.2	100	97	97	94	97	94	25
10	5.1	100	97	95	92	95	92	25
16	6.4	100	97	94	91	90	87	30
20	7.1	100	97	93	90	90	87	30
31.2	8.9	100	97	91	88	90	87	29
62.5	12.7	100	97	87	84	85	82	27
100	16	100	97	84	81	80	77	25
155	20	95	92	75	72	78	75	24
200	22.8	93	90	70	67	75	72	23
250	25.5	91	88	66	63	69	66	22
300	28	90	87	62	59	65	62	22
600	40	86	83	46	43	45	42	20
1000	52.1	82	79	30	27	40	37	20
1200	57.2	81	78	24	21	35	32	19
1400	62	80	77	18	15	30	27	19
1500	64.3	80	77	16	13	28	25	18