


N10a: UC^{FIBRE} I/O ST LSHF-FR C_{ca} 1.8KN

1800N, universal, ST, up to 432f, LWB, FireRes® sheath



GENERAL INFO

Universal indoor/outdoor cable metal-free for LAN, MAN and WAN backbones. With its FireRes® LSHF-FR sheathing this cable is ideal for mixed indoor and limited outdoor installation. It is equally suited for installation in ducts and on trays. This innovative cable is Class-Cca approved, highly flame retardant with gel-filled tubes and water-blocked characteristics, for use in public buildings with a high personal risk.

More information on fiber optic cable applications: [read more](#)

Latest version of this data sheet is available for download: [ProductFamily405131](#)

CERTIFICATIONS AND DESIGN STANDARDS



ISO/IEC 11801

EN 50173

EN 50575

IEC 60794-1-1

IEC 60794-6-10

Generic telecom cabling for customer premises
Information technology - Generic cabling systems
Cables in construction works subject to reaction to fire
Generic Specification Fibre Optic Cables
Family specification for universal indoor-outdoor cables

APPLICATION PROPERTIES

Resistant to UV	UV stabilised
Outdoor installation With rodent protection	Not applicable
Operation temperature (min) [°C]	-40 and (max) [°C] 70
Installation temperature (min) [°C]	-20 and (max) [°C] 60
Storage temperature (min) [°C]	-30 and (max) [°C] 60
Bending radius (rule)	During installation (loaded) = 20xOD, Permanent (unloaded) = 10xOD

MECHANICAL PROPERTIES

Crush	IEC 60794-1-21 E3	2,000 N/10cm
Max. tensile strength during installation	IEC 60794-1-21 E1	1,800 N
Permanent tensile strength	IEC 60794-1-21 E1	600 N
Impact test	IEC 60794-1-21 E4	20 N·m
Torsion test	IEC 60794-1-21 E7	5 cycles ±1turn
Kink	IEC 60794-1-21 E10	The cables do not form a kink when a loop is drawn together to a diameter 20 times the cable nominal diameter.


FIRE PROPERTIES

Flame retardant	acc. IEC/EN 60332-1-2, IEC/EN 60332-3-24
Halogen free	acc. IEC/EN 60754-2
Low smoke	acc. IEC/EN 61034-2
The reaction to fire according to the EN 50575	Cca - s1, d1, a1

* The measurement of smoke density of cables burning under defined conditions according to the IEC 61034-2 applies only to the 12fo up to 192fo counts.

CABLE CONSTRUCTION

Type of tube	Stranded construction with Ø2.3 mm gel-filled loose tubes with 12 fibres each for up 144fo and Ø2.8 mm gel-filled loose tubes with 24 fibres each for over 144fo cables.
Longitudinal water blocking cable	Yes
Rip cord	Yes
Material outer sheath	1.5mm, Low smoke zero halogen, FireRes®
Cable shape	Round
Cable marking example	DRAKA UCFIBRE I/O ST LSHF-FR Cca-s1-d1-a1 1.8 kN 'Fibre count' 'Fibre type' 'Fibre brand' 'Item No' 'Factory No' 'Batch Number' 'Meter mark' U-DQH 'Number of Elements' x 'Fibre count per element' 'Fibre family' 'Mode field diameter' /125 'Transmission Class'



IDENTIFICATION

Fibre colour code	1 Red	13 Red w/mark every 70mm
in accordance with IEC 60794-2 and VDE 0888 read more	2 Green	14 Green w/mark every 70mm
	3 Blue	15 Blue w/mark every 70mm
	4 Yellow	16 Yellow w/mark every 70mm
	5 White	17 White w/mark every 70mm
	6 Grey	18 Grey w/mark every 70mm
	7 Brown	19 Brown w/mark every 70mm
	8 Violet	20 Violet w/mark every 70mm
	9 Turquoise	21 Turquoise w/mark every 70mm
	10 Black	22 White w/mark every 35mm
	11 Orange	23 Orange w/mark every 70mm
	12 Pink	24 Pink w/mark every 70mm

Sheath color	Cable with SM fibres: BendBrightXSG.657.A2, BendBright G.657.A1 Yellow, RAL 1018
	Cable with mixed fibre types (hybrid) Blue, RAL 5015
	Cable with OM1 Grey, RAL 7037
	Cable with MaxCap-BendBright-OM2 Orange, RAL 2009
	Cable with MaxCap-BendBright-OM3 Aqua, RAL 6027
	Cable with MaxCap-BendBright-OM4 Erika-Violet, RAL 4003
	Cable with BendBright WideCap-OM5 Lime-Green, RAL 6039

CABLE DETAILS

Number of fibres	Number of fibres per tube	Nominal outer diameter [mm]	Min. bending radius, fixed [mm]	Min. permitted bending radius, during cable laying [mm]	Cable weight [kg/km]	Fire load [MJ/km]
12	12	10.4	104	208	95	1,445
24	12	10.4	104	208	98	1,331
48	12	10.4	104	208	105	1,461
72	12	10.4	104	208	115	1,591
96	12	11.8	118	236	145	1,970
144	12	15	150	300	240	2,718
288	24	18	180	360	330	4,082
432	24	18.2	182	364	300	5,322

ORDERING DETAILS

Product name	Number of fibres	Category (fibre)	Fibre datasheet	Colour outer sheath	DOP number	SAP code
UCFIBRE I/O ST LSHF-FR C 1.8kN 24 SM7A2	24	OS2	C24	Yellow	-	N10a-24SM7A2
UCFIBRE I/O ST LSHF-FR C 1.8kN 48 SM7A2	48	OS2	C24	Yellow	-	N10a-48SM7A2
UCFIBRE I/O ST LSHF-FR B2 1.8kN 96 SM7A2	96	OS2	C24	Yellow	-	N10a-96SM7A2
UCFIBRE I/O ST LSHF-FR C 1.8kN 144 SM7A2	144	OS2	C24	Yellow	-	N10a-144SM7A2
UCFIBRE I/O ST LSHF-FR C 1.8kN 288 SM7A2	288	OS2	C24	Yellow	-	N10a-288SM7A2
UCFIBRE I/O ST LSHF-FR C 1.8kN 432 SM7A2	432	OS2	C24	Yellow	-	N10a-432SM7A2
UCFIBRE I/O ST LSHF-FR C 1.8kN 12 SM7A1	12	OS2	C53	Yellow	-	N10a-12SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 24 SM7A1	24	OS2	C53	Yellow	-	N10a-24SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 72 SM7A1	72	OS2	C53	Yellow	-	N10a-72SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 96 SM7A1	96	OS2	C53	Yellow	-	N10a-96SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 288 SM7A1	288	OS2	C53	Yellow	-	N10a-288SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 432 SM7A1	432	OS2	C53	Yellow	-	N10a-432SM7A1
UCFIBRE I/O ST LSHF-FR C 1.8kN 24 OM3B	24	OM3	C31	Turquoise	-	N10a-24OM3B
UCFIBRE I/O ST LSHF-FR C 1.8kN 48 OM3B	48	OM3	C31	Turquoise	-	N10a-48OM3B
UCFIBRE I/O ST LSHF-FR C 1.8kN 96 OM3B	96	OM3	C31	Turquoise	-	N10a-96OM3B
UCFIBRE I/O ST LSHF-FR C 1.8kN 144 OM3B	144	OM3	C31	Turquoise	-	N10a-144OM3B
UCFIBRE I/O ST LSHF-FR C 1.8kN 288 OM3B	288	OM3	C31	Turquoise	-	N10a-288OM3B
UCFIBRE I/O ST LSHF-FR C 1.8kN 12 OM4B	12	OM4	C32	Erika-violet	-	N10a-12OM4B
UCFIBRE I/O ST LSHF-FR C 1.8kN 24 OM4B	24	OM4	C32	Erika-violet	-	N10a-24OM4B
UCFIBRE I/O ST LSHF-FR C 1.8kN 96 OM4B	96	OM4	C32	Erika-violet	-	N10a-96OM4B
UCFIBRE I/O ST LSHF-FR C 1.8kN 144 OM4B	144	OM4	C32	Erika-violet	-	N10a-144OM4B
UCFIBRE I/O ST LSHF-FR C 1.8kN 24 OM5B	24	OM5	C39	Lime green	-	N10a-24OM5B

ORDERING DETAILS

Product name	Number of fibres	Category (fibre)	Fibre datasheet	Colour outer sheath	DOP number	SAP code
UCFIBRE I/O ST LSHF-FR C 1.8kN 96 OM5B	96	OM5	C39	Lime green	-	N10a-96OM5B
UCFIBRE I/O ST LSHF-FR C 1.8kN 144 OM5B	144	OM5	C39	Lime green	-	N10a-144OM5B

**DoP Numbers are per product code and any DoP number proves CPR approval for the cable. DoP files can be downloaded from the website: [DoP](#)*

© PRYSMIAN 2025, all rights reserved. All sizes and values without tolerances are reference values. Specifications are for product as supplied by PRYSMIAN: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PRYSMIAN. The information is believed to be correct at the time of issue. PRYSMIAN reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by PRYSMIAN.