


JE-H(ST)H SIENOPYR E30 FE180 225V

Fire-resistant and screened signal cable for fixed installation



DESCRIPTION

Fire-resistant, halogen-free and screened signaling cable for indoor fixed installation of fire alarms, detectors and emergency communications systems. During a fire the cable will uphold its circuit integrity for 30 minutes.

JE-H(ST)H E30 225V is registered in the Ecolabel database over building materials, that can be used /included in Svanemærket certified buildings.

CERTIFICATION, APPROVAL & STANDARD



IEC 60331-2

EN 50200

EN 50362

ROHS

REACH

Tests for electric cables under fire conditions below 20mm in diameter

Method of test for resistance to fire of unprotected small cables for use in emergency circuits

Fire resistance test - cables for emergency power circuits

RoHS compliance - restriction of hazardous substances directive

Regulation concerning the Registration, Evaluation, Authorisation and Restriction of CHemicals.

CONSTRUCTION

Conductor material

Copper

Conductor surface

Bare

Core insulation material

Halogenfree polymer

Drain wire

Yes

Screen construction

Metal tape

Screen material

Aluminium

Material outer sheath

Halogenfree polymer

Cable shape

Round

ELECTRICAL PROPERTIES

Nominal voltage U ₀ [V]	225
Nominal mutual capacitance [pF/m]	100
Capacitance unbalance (max) [pF/m]	200

FIRE PROPERTIES

Circuit integrity	E 30
Insulation integrity	FE 180
Insulation integrity (acc. IEC 60331)	Yes
Self-extinguishing	Yes
Flame retardant	In accordance with EN/IEC 60332-1-2
Halogen free	acc. IEC/EN 60754-1/2
Low smoke	acc. IEC/EN 61034-2

THERMAL PROPERTIES

Max. conductor temperature [°C]	70
Max. outer temperature, fixed installation [°C]	-30
Permitted cable outer temperature after assembling without vibration (max) [°C]	70
Permitted cable outer temperature during assembling/handling (min) [°C]	-5
Permitted cable outer temperature during assembling/handling (max) [°C]	50

MECHANICAL PROPERTIES

Bending radius (rule)	During installation with traction 7,5 x D Single bend without traction 2,5 x D
-----------------------	--------------------------------------------------------------------------------

APPLICATION PROPERTIES

UV resistant	No
Outdoor installation	No
Underground installation	No
Suitable as telephone cable	Yes
Suitable as computer data cable	Yes
Suitable as signalling cable	Yes

© Prysmian Denmark A/S. All rights reserved.

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian; any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without notice.

This specification is not contractually valid unless specifically authorised by Prysmian.

DELIVERY INFORMATION

Basic construction	Conductor category	Colour outer sheath	Standard packaging quantity	SAP code	DOP number	EAN-code (GTIN)
2x2x0,8+0,8 mm	Class 1 = solid	Orange	500	20160178		4250248100567
4x2x0,8+0,8 mm	Class 1 = solid	Orange	500	20002235		4250248100550
8x2x0,8+0,8 mm	Class 1 = solid	Orange	500	20002236		4250248100673

MECHANICAL DATA

Basic construction	Number of cores	AWG size	Diameter conductor [mm]	Nominal outer diameter [mm]	Cable weight [kg/km]	Fire load [MJ/km]	Max. tensile strength during installation [kN]
2x2x0,8+0,8 mm	4		0.8	7.5	68	72	
4x2x0,8+0,8 mm	8		0.8	9.3	107	104	
8x2x0,8+0,8 mm	16		0.8	11.4	174	151	

ELECTRICAL DATA

Basic construction	Conductor resistance at 20° C [Ohm/km]	Loop resistance [Ohm]	Characteristic impedance [Ohm]	Coupling attenuation [dB]	Nominal operation capacitance [nF/km]
2x2x0,8+0,8 mm	36.6	73.2			100
4x2x0,8+0,8 mm	36.6	73.2			100
8x2x0,8+0,8 mm	36.6	73.2			100